Rittal – The System.

Faster – better – everywhere.



SK 3201.990
Connection set

State: 23/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3201.990 - Connection set for air-water heat exchangers

For professional laying of water connections and regulation of volumetric flow.

Features

Model No.	SK 3201.990
Product description	For professional laying of water connections and regulation of volumetric flow. The pressure hoses may be cut to length individually, depending on the application.
Material	Water-carrying parts EPDM/brass
Supply includes	Hose for water return Hose for water inlet including regulator valve for regulating the volumetric flow (setting range 3 to 12 l/min) Assembly parts
Length	3,600 mm
Water connections	G ⅜" internal thread
To fit Model No.	3209.XX0 3210.XX0 3216.480 3363.XX0 3364.XX0 3373.XX0 3374.XX0 3375.XX0 3319.000 / 3419.000 3320.200 / 3420.200
Dimensions	Length: 3,600 mm
Permissible operating pressure (p. max.)	1: 10 bar
Packs of	1 pc(s).
Net weight	4 kg

© Rittal 2026

Features

Gross weight	4.58 kg
Customs tariff number	85444290
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK Connection set, for air/water heat exchanger, G 3/8" internal thread, Length: 3600 mm

© Rittal 2026