

Flange Mount Disconnect TS8 Enclosures

Cross reference chart

	FMD Part Number	Previous version cross reference	Dimensions HxWxD	Sidewalls Part number	Mounting Panel (included) HxW	4" (100mm) high flex block plinths Part numbers			4" (100mm) high plinths Part numbers	
			mm	pair	mm	front & rear	sides	corners	front & rear	sides
Single Door	9951.134	8984.500	1800x0800x0400	8184.235	1696x0699	8100.800	8100.400	8100.000	8601.800	8601.040
	9951.135	8985.500	1800x0800x0500	8185.235	1696x0699	8100.800	8100.500	8100.000	8601.800	8601.050
	9951.136	8980.500	1800x1000x0500	8185.235	1696x0899	8100.010	8100.500	8100.000	8601.100	8601.050
	9951.142	8905.500	2000x0800x0500	8105.235	1896x0699	8100.800	8100.500	8100.000	8601.800	8601.050
	9951.143	8906.500	2000x0800x0600	8106.235	1896x0699	8100.800	8100.600	8100.000	8601.800	8601.060
	9951.144	8908.500	2000x0800x0800	8108.235	1896x0699	8100.800	8100.800	8100.000	8601.800	8601.080
	9951.145	8995.500	2000x1000x0500	8105.235	1896x0899	8100.010	8100.500	8100.000	8601.100	8601.050
	9951.146	8996.500	2000x1000x0600	8106.235	1896x0899	8100.010	8100.600	8100.000	8601.100	8601.060
	9951.153	8956.500	2200x0800x0600	8126.235	2096x0699	8100.800	8100.600	8100.000	8601.800	8601.060
9951.154	8958.500	2200x1000x0500	8125.235	2096x0899	8100.010	8100.500	8100.000	8601.100	8601.050	
Double Door	9951.138	8901.610	1800x1600x0500	8185.235	1696x1499	8100.160	8100.500	8100.000	8601.920	8601.050
	9951.140	8901.630	1800x1800x0500	8185.235	1696x1699	8100.180	8100.500	8100.000	8901.920	8601.050
	9951.147	8901.650	2000x1600x0500	8105.235	1896x1499	8100.160	8100.500	8100.000	8601.920	8601.050
	9951.148	8901.660	2000x1600x0600	8106.235	1896x1499	8100.160	8100.600	8100.000	8601.920	8601.060
	9951.150	8901.680	2000x1800x0500	8105.235	1896x1699	8100.180	8100.500	8100.000	8901.920	8601.050
	9951.151	8901.690	2000x1800x0600	8106.235	1896x1699	8100.180	8100.600	8100.000	8901.920	8601.060