

Rittal – The System.

Faster – better – everywhere.

▶ CP Command Panel HMI Housing with Handle Strips



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

www.rittal.us



CP Command Panel HMI Housing with Handle Strips



Elegant design with high functionality

This new and improved HMI Housing features:

- Modern, attractive design
- Compatibility with Rittal system internal mounting accessories
- Ease of assembly to CP 60/120/180 support arm system

Rittal's new HMI housing with Handle Strips offers:

- Attractive design compatible with the new CP 60/120/180 support arm system
- Rear or front access versions for easy servicing
- Easy to remove and machine aluminum front panel
- 10 sizes available off-the-shelf
- Protection category IP55/CSA NEMA12
- Double bit insert cam lock with integral door runners
- Uniform interior installation via Rittal system accessories
- 5" (130mm) diameter cutout enables one person assembly with CP 60/120/180 support arm systems and pedestal stands
- Both top or bottom installations are possible based on enclosure orientation
- Attractive and functional built in handles

This new updated HMI Housing design replaces the former platforms:

- Command Panel housing with door
- Command Panel based on AE with handle strips
- Operator housing with display panel front

| Part Number | Description | Height | Width | Depth | Servicing Access |
|-------------|-------------------------------------|---------------|--------------|---------------|------------------|
| 6320000 | 300W X 200H X 155D MM W/ REAR DOOR | 200 mm (7.9") | 300 mm (12") | 155 mm (6.1") | From the rear |
| 6315100 | 300W X 300H X 210D MM W/ FRONT DOOR | 300 mm (12") | 300 mm (12") | 210 mm (8.3") | From the front |
| 6315200 | 380W X 300H X 210D MM W/ FRONT DOOR | 300 mm (12") | 380 mm (15") | 210 mm (8.3") | From the front |
| 6315300 | 380W X 380H X 210D MM W/ FRONT DOOR | 380 mm (15") | 380 mm (15") | 210 mm (8.3") | From the front |
| 6320300 | 380W X 380H X 210D MM W/ REAR DOOR | 380 mm (15") | 380 mm (15") | 210 mm (8.3") | From the rear |
| 6315400 | 500W X 500H X 210D MM W/ FRONT DOOR | 380 mm (15") | 600 mm (24") | 210 mm (8.3") | From the rear |
| 6320400 | 500W X 500H X 210D MM W/ REAR DOOR | 500 mm (20") | 500 mm (20") | 210 mm (8.3") | From the front |
| 6320500 | 600W X 380H X 210D MM W/ REAR DOOR | 500 mm (20") | 500 mm (20") | 210 mm (8.3") | From the rear |
| 6320600 | 600W X 600H X 210D MM W/ REAR DOOR | 600 mm (24") | 600 mm (24") | 210 mm (8.3") | From the front |
| 6315600 | 600W X 600H X 210D MM W/ FRONT DOOR | 600 mm (24") | 600 mm (24") | 210 mm (8.3") | From the rear |

Rittal Corporation

Woodfield Corporate Center • 425 N. Martingale Road, Suite 400 • Schaumburg, IL 60173 • USA
 1 Rittal Place • Urbana, OH 43078 • USA
 Phone: 937-399-0500 • Toll-Free: 800-477-4000
 E-mail: rittal@rittal.us • Online: www.rittal.us

2/16 • US277

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

