

Rittal – The System.

Faster – better – everywhere.

Micro Data Center Level B – DK 7999.709

Date : Sep 20, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Micro Data Center Level B – DK 7999.709

created: 20.09.2020 build on www.rittal.com/lt-en



Product description

Benefits:	TS 8 supporting structure as frame Front and rear 482.6 mm (19") level with air baffle plates for optimum air routing and thus efficient cooling included in the supply as standard Weight reduction compared with Modular Safe Level E Simple, fast assembly
Applications:	Solid protection against potential physical threats for IT components Targeted configuration components transform the safe into a complete, compact data centre.
Material:	Sheet steel, coated
Colour:	Enclosure: RAL 7035 Service door: RAL 7035 Operator door: RAL 9005
Protection category IP to IEC 60 529:	IP 56
Supply includes:	Safe with integral TS 8 frame Front and rear 482.6 mm (19") level Adjusted air baffle plates Every side element is prepared for one cable entry at the bottom and one cable entry at the top Operator and service door with swing-lever handle and semi-cylinder
Options:	Choice of door hinges Twin-walled doors Different cable entry systems Cable entry in the top and base unit Different lock variants Supporting structure with fire protection
Protection standards:	Fire resistance class EI 90/F 90 to DIN EN 1363-1: 1999 based on DIN EN 4102-2:1997

The critical connection points were tested as a system
 Burglar resistance RC 2, tool attack analogous to DIN EN 1630/2011-09/RC 2
 The single safe was tested as a system with single-leaf doors and mechanical lock
 Smoke protection based on DIN EN 1634-3:2005-01
 The single safe was tested as a system with single-leaf doors and mechanical lock

Standard protection from:	Fire Extinguishing water Vandalism Unauthorised access Dust Theft/burglary
Note:	Project planning on request
Product features	
Installation height for components:	47 U
Dimensions:	Width: 1115 mm Height: 2405 mm
Clearances:	Clearance height: 2200 mm Clearance depth: 1260 mm
Number of doors:	2
Packs of:	1 pc(s).
EAN:	4028177717091
Customs tariff number:	94032080
ETIM 7.0:	EC002499
ETIM 6.0:	EC002499
eCl@ss 8.0/8.1:	27180207
eCl@ss 6.0/6.1:	27180207
Product description:	LS Micro Data Centre, Level B