Rittal – The System.

Faster – better – everywhere.



# SM 6450.010
# TFT monitor

State: 2026.11.24 (Source: www.rittal.com/lt-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SM 6450.010 - TFT monitor

Installation variant for surfaces and command panels.

## Features

| | |
|---|---|
| Model No. | SM 6450.010 |
| Design | without touchscreen |
| Product description | Installation variant for surfaces and command panels. |
| Benefits | High-quality industrial design<br>Reduced installation work thanks to integral front frame<br>No additional ventilation required<br>Very small installation depth (45 mm) |
| Material | Front frame: Aluminium |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Seal<br>Hex nuts (for installation in surfaces)<br>VGA cable<br>Threaded bolt M5, for rear mounting<br>Touch variants additionally with integral connection cable and CD-ROM driver<br>With anti-reflection coated safety glass screen. |
| Dimensions | Width: 430 mm<br>Height: 343 mm |
| Interfaces | VGA (D-Sub HD 15-pole)<br>DVI-D |
| Operating temperature range | 0 °C...50 °C |
| Storage temperature range | -40 °C...85 °C |
| Display brightness | 400 cd/m² |
| Contrast ratio | 700 : 1 |
| Diagonal | 15" |

© Rittal 2026

# Features

| | |
|---|---|
| Hours of operation | 50,000 h |
| On Screen Display (OSD) | Operating buttons at the rear |
| Reading angle left/right | 80 ° |
| Resolution of display | 1024 x 768 pixels |
| Power consumption Pel | With DC: 15 W |
| H-Sync. (min./max.) | 31.4 - 80 kHz |
| V-Sync. (min./max.) | 60 - 75 Hz |
| Number of colours | 16.7 |
| Resolution of controller | VGA<br>SVGA<br>XGA |
| Packs of | 1 pc(s). |
| Net weight | 6.4 kg |
| Gross weight | 6.52 kg |
| Customs tariff number | 85286200 |
| ETIM 9 | EC001428 |
| ECLASS 8.0 | 19200201 |
| Product description | SM TFT monitor, 15" |

# Approvals

| | |
|---|---|
| Explanations | Declaration of conformity |