
Rittal – The System.

Faster – better – everywhere.



# AS 4051.696
# Wire end ferrules

State: 24/11/2026 (Source: www.rittal.com/ro-ro)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AS 4051.696 - Wire end ferrules on a reel

With plastic collar.

## Features

| | |
|---|---|
| Model No. | AS 4051.696 |
| Product description | With plastic collar. |
| Technical specifications | Heat-resistant to 105 °C |
| Material | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene |
| Colour | Grey |
| Length | 10 mm |
| AWG | 18 |
| Internal diameter | 2,8 mm |
| For cross-section | 0,75 mm² |
| DIN colour code | Yes |
| Note | UL-certified in conjunction with the relevant tools, such as crimping machines. |
| Standards | AEH DIN 46228 |
| Delivery form | Taped |
| Packs of | 5.000 pc(s). |
| Net weight | 5 kg |
| Customs tariff number | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |
| Product description | Wire end ferrules 0.75 mm² x 10 mm AWG 18, packs of 5,000 pc(s)., colour: grey, delivery form: on belt (in accordance with the DIN colour code) |

© Rittal 2026

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |