Rittal – The System.

Faster – better – everywhere.

IT 3659.181

Teleskopické lišty pre servery

State: 23.5.2026 (Source: rittal.com/sk-sk)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

IT 3659.181 - Teleskopické lišty pre servery pre IT skriňové systémy a IT skrinky

Ensure optimum access to the servers, even when built-in. For servers with a maximum width of 430 mm.

Features

Obj. č.	IT 3659.181
Prevedenie	Pre vzdialenosť medzi rovinami 470,65 – 599,65 mm
Materiál	Oceľový plech
Zaťažiteľnosť	30 kg
Poznámka	Iba v spojení s profilovými lištami tvaru L
Vhodné pre	Typ skrine: TS TS IT VX VX IT HÍbka: = 600 mm
Balenie	2 pc(s).
Netto hmotnosť	2,3 kg
Brutto hmotnosť	2,62 kg
PCF per pack (cradle-to-gate)	5,1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Číslo colnej sadzby	73269098
ETIM 9	EC002620

Features

ETIM 8	EC002620
ECLASS 8.0	27189261
Popis výrobku	Teleskopické lišty pre servery TS, TS IT, VX, VX IT, pre hĺbku 600 mm, výsuv: 490 mm, pre servery s maximálnou šírkou 430 mm