
Rittal – The System.

Faster – better – everywhere.



SV 9666.757

Mounting angles ISV

State: 24/11/2026 (Source: www.rittal.com/uk-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9666.757 - Mounting angles ISV for AX

For vertical sub-division of the support frame in the AX/AE enclosure.

Features

Model No.	SV 9666.757
Product description	For vertical sub-division of the support frame in the enclosure.
Material	Sheet steel
Surface finish	Zinc-plated
Dimensions	Height: 1,050 mm
Size	Height units (U) @ 150 mm: 7
Packs of	2 pc(s).
Net weight	1.248 kg
Gross weight	1.448 kg
PCF per pack (cradle-to-gate)	5.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	39269097
ETIM 9	EC002270
ECLASS 8.0	27400613
Product description	SV Mounting angle (ISV), 7 U (1050 mm), for AE

© Rittal 2026