Rittal – The System.

Faster – better – everywhere.



# EL 2094.500

# Captive nut

State: 11/25/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# EL 2094.500 - Captive nut

Captive nut, with M5 thread, with contact

## Features

| | |
|---|---|
| Model No. | EL 2094.500 |
| Version | With contact |
| Product description | To fasten slide-in electronic equipment, 482.6 mm (19") installed equipment and blanking plates to profile rails. Used with profile plate thicknesses 0.8 – 2.5 mm. Either with or without contacting the installed equipment with the 482.6 mm (19") profile/housing. |
| Dimensions | Thread: M5 |
| For material thicknesses | 0.8 - 2.5 mm<br>0.03 - 0.1 ″ |
| Packaging unit | 50 pc(s). |
| Net weight | 0.2 kg |
| Gross weight | 0.25 kg |
| Customs tariff number | 73181692 |
| ETIM 9 | EC002358 |
| ETIM 8 | EC002358 |
| ECLASS 8.0 | 23110815 |
| Product description | EL Captive nuts, M5, With contact, For metal thickness: 0,8-2 mm |

© Rittal 2026