Rittal – The System.

Faster – better – everywhere.



AX 2741.010

Operating panel

State: 11/29/2026 (Source: www.rittal.com/us-en)

AX 2741.010 - Operating panel for AX

For external mounting on AX enclosure instead of a door and on surfaces. Frame structure with internal corner connectors, 3 mm thick aluminum plate, secured from the inside.

Features

Model No.	AX 2741.010
Product description	For mounting on AX housing instead of door and on surfaces. Frame structure with internal corner connectors, 3 mm thick aluminum plate, secured from inside.
Material	Aluminum, natural anodized
Supply includes	Aluminum frame Display panel Hinges Brackets
Protection category IP to EN 60 529	IP 54
Suitable for Model No.	1004.000 1011.000 1031.000
Note	During installation, the cam lock is required in place of the door
Suitable for	Enclosure type: AX Width: = 380 mm Height: = 300 mm Enclosure type: AX Width: = 15 ″ Height: = 11.8 ″
Dimensions	Width: 377 mm Height: 297 mm Depth: 36 mm Width: 14.8 ″ Height: 11.7 ″ Depth: 1.42 ″

© Rittal 2026

Features

Dimensions of aluminium plate	Width: 323 mm Height: 243 mm Width: 12.7 ″ Height: 9.57 ″
Area available for population	Width: 307 mm Height: 227 mm Width: 12.1 ″ Height: 8.94 ″
Packaging unit	1 pc(s).
Net weight	2.043 kg
Gross weight	2.18 kg
Customs tariff number	76169990
ETIM 9	EC000747
ETIM 8	EC000747
ECLASS 8.0	27182204
Product description	FT Operating panel, WHD: 377x297x36 mm, for AX enclosures instead of the door and surfaces