Rittal – The System.

Faster – better – everywhere.



AX 2744.010

Operating panel

State: 11/29/2026 (Source: www.rittal.com/us-en)

AX 2744.010 - Operating panel for AX

For external mounting on AX enclosure instead of a door and on surfaces. Frame structure with internal corner connectors, 3 mm thick aluminum plate, secured from the inside.

Features

Model No.	AX 2744.010
Product description	For mounting on AX housing instead of door and on surfaces. Frame structure with internal corner connectors, 3 mm thick aluminum plate, secured from inside.
Material	Aluminum, natural anodized
Supply includes	Aluminum frame Display panel Hinges Brackets
Protection category IP to EN 60 529	IP 54
Suitable for Model No.	1009.000 1039.000 1339.000
Note	During installation, the cam lock is required in place of the door
Suitable for	Enclosure type: AX Width: = 600 mm Height: = 380 mm Enclosure type: AX Width: = 23.6 ″ Height: = 15 ″
Dimensions	Width: 597 mm Height: 377 mm Depth: 36 mm Width: 23.5 ″ Height: 14.8 ″ Depth: 1.42 ″

© Rittal 2026

Features

Dimensions of aluminium plate	Width: 543 mm Height: 323 mm Width: 21.4 ″ Height: 12.7 ″
Area available for population	Width: 527 mm Height: 307 mm Width: 20.7 ″ Height: 12.1 ″
Packaging unit	1 pc(s).
Net weight	3.131 kg
Gross weight	3.331 kg
Customs tariff number	76169990
ETIM 9	EC000747
ETIM 8	EC000747
ECLASS 8.0	27182204
Product description	FT Operating panel, WHD: 597x377x36 mm, for AE enclosures instead of the door and surfaces