Rittal – The System.

Faster – better – everywhere.



# SK 3240.200
# Outlet Filters

State: 11/29/2026 (Source: www.rittal.com/us-en)

# SK 3240.200 - Outlet Filters Standard

For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure.



## Features

| | |
|---|---|
| Model No. | SK 3240.200 |
| Product description | For ventilation by convection, an outlet filter can be installed in the upper and lower sections of the enclosure. |
| Material | ABS |
| Color | RAL 7035 |
| Supply includes | Outlet Filters<br>Chopped fiber filter mat |
| Mounting cut-out | Width of opening: 224 mm<br>Cut-out height: 224 mm<br>Width of opening: 8.82 ″<br>Cut-out height: 8.82 ″ |
| Suitable for Model No. | 3240.1xx/3240.5xx/3241.1xx/3241.5xx |
| Dimensions | Width: 255 mm<br>Height: 255 mm<br>Depth: 25 mm<br>Width: 10 ″<br>Height: 10 ″<br>Depth: 0.98 ″ |

© Rittal 2026

# Features

| | |
|---|---|
| Protection category NEMA | Type 12 with chopped fiber filter/pleated filter<br>Type 3<br>Type 3R<br>Type 4<br>Type 4X with chopped fiber filter/pleated filter and hose-proof hood |
| Protection category IP to IEC 60 529 | IP 54 with chopped fiber filter/pleated filter<br>IP 55 with pleated filter and absorber mat<br>IP 56 with chopped fiber filter/pleated filter and hose-proof hood |
| Packaging unit | 1 pc(s). |
| Net weight | 0.56 kg |
| Gross weight | 0.582 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| Product description | SK outlet filter, Standard, WHD: 255 x 255 x 25 mm |

# Approvals

| | |
|---|---|
| Approvals | CSA<br>UL + C-UL - FTTA<br>UR + C-UR (recognized) |