


# Rittal – The System.

Faster – better – everywhere.



## AS 4050.080 Clamping frame

State: 13/03/2026 (Source: [rittal.com/au-en](https://www.rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.080 - Clamping frame

Parallel machining of enclosures in the cube machining zone of Perforex machining centres BC and Perforex milling terminals MT for shorter setup times and enhanced productivity.

## Features

|                                                           |                                                                                                                                            |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                                                 | AS 4050.080                                                                                                                                |
| Design                                                    | Pneumatic clamping device                                                                                                                  |
| Product description                                       | Enables parallel cube machining of enclosures on Perforex machining centres BC and Perforex milling terminals MT.                          |
| Possible number of terminal Boxes for parallel processing | 3                                                                                                                                          |
| Note                                                      | Use of the clamping frame (Model No. 4050.080) in the machining centre BC (Model No. 4050.230) is only possible with the two-door variant. |
| To fit Model No.                                          | 4050.108<br>4050.230<br>4055.925<br>4055.926                                                                                               |
| Suitable for                                              | Perforex BC 1008 HS<br>Perforex BC 2014 HS<br>Perforex MT 2201<br>Perforex MT 2201 S                                                       |
| Dimensions of clampable enclosures max.                   | Width: 510 mm<br>Height: 510 mm<br>Depth: 600 mm                                                                                           |
| Dimensions of clampable enclosures min.                   | Width: 80 mm<br>Height: 100 mm<br>Depth: 80 mm                                                                                             |
| Packs of                                                  | 1 pc(s).                                                                                                                                   |
| Net weight                                                | 25 kg                                                                                                                                      |
| Gross weight                                              | 25 kg                                                                                                                                      |
| Customs tariff number                                     | 84669360                                                                                                                                   |

# Features

|                     |                                                                                                                                                                                                               |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ETIM 9              | EC003010                                                                                                                                                                                                      |
| ETIM 8              | EC003010                                                                                                                                                                                                      |
| ECLASS 8.0          | 36609190                                                                                                                                                                                                      |
| Product description | AS Multiple fastening, BC 1008/2014, Clamping frame for several small enclosures, - 3 clamping positions in the frame, - Pneumatic clamping device, - Min. enclosure dimensions (W x H x D): 80 x 100 x 80 mm |