Rittal – The System.

Faster – better – everywhere.



# TS 8602.000

# Base/plinth components, front and rear, 200 mm

State: 11/26/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 8602.000 - Base/plinth components, front and rear, 200 mm Carbon steel, for TS, TS IT, SE, CM, TP, PC, IW, TE

Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry.

## Features

| | |
|---|---|
| Model No. | TS 8602.000 |
| Version | Solid |
| Product description | Base/Plinth component consisting of one trim panel and two pre-assembled corner pieces. On 200 mm high base/plinth components, one trim panel is in two parts to allow for cable entry. |
| Material | Base/plinth components: Carbon steel<br>Cover caps: Plastic |
| Surface finish | Spray-finished |
| Color | RAL 7022<br>Cover caps: RAL 9005 |
| Supply includes | 2 base/plinth components<br>4 cover caps<br>Assembly components |
| Dimensions | Height: 200 mm<br>Height: 7.87 ″ |

© Rittal 2026

# Features

| | |
|---|---|
| Suitable for | Enclosure type: TS: = 1,000 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT<br>Enclosure type: TS: = 39.4 ″<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT |
| Packaging unit | 2 pc(s). |
| Net weight | 9.1 kg |
| Gross weight | 9.3 kg |
| Customs tariff number | 94039910 |
| ECLASS 8.0 | 27182003 |
| Product description | TS Base/plinth component, front and rear, H: 200 mm, for W: 1000 mm, RAL 7022, sheet steel |

© Rittal 2026