Rittal – The System.

Faster – better – everywhere.

TS 8801.330

TS Roof Plates

State: 3/15/2026 (Source: rittal.com/us-en)

ENCLOSURES POWER DISTRIBUTION CLIMATE CONTROL IT INFRASTRUCTURE SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8801.330 - TS Roof Plates

Features

Model No.	TS 8801.330
Product description	For installing roof-mounted cooling units and roof-mounted air/ water heat exchangers. The cut-outs in the roof plate are arranged so that the roof-mounted cooling units are centered on the enclosure.
Benefits	Simple, fast mounting
Material	Carbon steel
Color	RAL 7035
Supply includes	Assembly components
Mounting cut-out	Width:490 mm Depth:390 mm Width:19.3 ˝ Depth:15.4 ˝
Distance cut-out to back	61.3 mm 2.41 ˝
Note	When mounting cooling units on the roof plate 8801.310 there may be a collision with the transportation eyebolts of the enclosure. For this reason, roof fastening screws are supplied loose with the roof plates. Attachment to the roof plate 8801.310 is from the inside using metal brackets and retaining clamps.
Suitable for Model No.	3209.... 3210.... 3383.... 3384.... 3385.... 3273....

Features

Dimensions	Width: 767.5 mm Height: 13 mm Depth: 567.5 mm Width: 30.2 ˝ Height: 0.51 ˝ Depth: 22.3 ˝
Suitable for	Enclosure type: TS Width: = 800 mm Depth: = 600 mm Enclosure type: TS Width: = 31.5 ˝ Depth: = 23.6 ˝
Packaging unit	1 pc(s).
Net weight	5.095 kg
Gross weight	5.363 kg
Customs tariff number	73269098
ECLASS 8.0	27182405
Product description	TS roof plates, for WD: 800 x 600 mm

Approvals

Certificates	EAC