Rittal – The System.

Faster – better – everywhere.



TS 9969.582

3-part EL NEMA 12 enclosure

State: 11/28/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 9969.582 - 3-part EL NEMA 12 enclosure with punched rails

The Rittal NEMA 12 3-Part EL wallmount enclosure is ideal for small networks or floor distribution in environments that require a high degree of security and a high industrial protection rating.

Features

Model No.	TS 9969.582
Product description	All standard models feature usable panel heights from 12U to 21U and ensure safe packaging for sensitive components as well as protection from the environment and from unauthorized access.
Material	Wall and hinged part: carbon steel, 16 ga (15 mm) Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Color	Wall and hinged part: RAL 7035 Viewing door: RAL 7035/7015 (slate gray)
Supply includes	Wall section Hinged part with 25 mm hole pattern of holes in the front and rear frame Designer viewing door Security lock 3524 E Comfort handle and 2-point lock for 18-21 U Wall section: Flange (gland) plate, solid, top and bottom Wall section: 2 vertical punched rails Horizontal C rail for cable clamping Hinged part: 19" (482.6 mm) profile rails, fully dept adjustable Wall mounting bracket, 10 mm (0.39 in.)
Clearances	Clearance width: 502 mm Clearance height: 949 mm Clearance width: 19.8 ″ Clearance height: 37.4 ″
Clearance height	949 mm 37.4 ″

Features

Depth hinged part	445 mm 17.5 ″
Depth of wall section	135 mm 5.31 ″
Clearance width	502 mm 19.8 ″
Load capacity of hinged part (static)	75 kg 165.3 lb.
Dimensions	Width: 600 mm Height: 1,016 mm Depth: 600 mm Width: 23.6 ″ Height: 40 ″ Depth: 23.6 ″
Packaging unit	1 pc(s).
Net weight	122.798 lb
Gross weight	122.798 lb
Customs tariff number	9403200082

© Rittal 2026