Rittal – The System.

Faster – better – everywhere.



# TS 9977.467

# TS 8 freestanding enclosures

State: 11/27/2021 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 9977.467 - TS 8 freestanding enclosures Stainless steel

Baying systems TS 8 with mounting plate. Protection category IP 66 (UL Type 4X). Manufactured in stainless steel 1.4404 (AISI 316L) Enclosure widths include 600 and 800 mm.





## Features

| | |
|---|---|
| Model No. | TS 9977.467 |
| Material | Enclosure frame: Stainless steel 1.4404 (AISI 316L), 1.5 mm<br>Roof: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior brushed<br>Door: Stainless steel 1.4404 (AISI 316L), 2.0 mm, exterior brushed<br>Rear panel: Stainless steel 1.4404 (AISI 316L), 1.5 mm, exterior brushed<br>Gland plate: Stainless steel 1.4404 (AISI 316L), 2.5 mm |
| Surface finish | Enclosure frame and base plates: Uncoated<br>Door, roof and rear panel: Exterior brushed, grain size 400<br>Mounting panel: Zinc-plated |
| Supply includes | Gland plate<br>Padlockable handle |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 800 mm<br>Height: 2,000 mm<br>Depth: 600 mm<br>Width: 31.5 ″<br>Height: 78.7 ″<br>Depth: 23.6 ″ |
| Packaging unit | 1 pc(s). |
| Net weight | 234.996 lb |
| Gross weight | 234.996 lb |
| Customs tariff number | 9403200082 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |