

# Rittal – The System.

Faster – better – everywhere.



## CX 6702.000

## CX pedestal

State: 22/05/2026 (Source: [rittal.com/au-en](http://rittal.com/au-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CX 6702.000 - CX pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



## Features

|                 |   |
|-----------------|---|
| Model No.       | CX 6702.000   |
| Design          | Pedestal  |
| Material        | Enclosure: Sheet steel 1.5 mm<br>Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal<br>Mounting plate: Sheet steel, 2.5 mm                |
| Surface finish  | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting plate: Zinc-plated                               |
| Colour          | RAL 7035  |
| Supply includes | Enclosure open at top<br>Door or double-door at front, with 3-point locking system<br>Mounting plate<br>Gland plates<br>Lock: 3 mm double-bit |
| Dimensions      | Width: 1,200 mm<br>Height: 675 mm<br>Depth: 400 mm  |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions mounting plate (W x H)   | 1,120 mm x 625 mm   |
| Number of doors                     | 2   |
| Door opening angle                  | 130°  |
| IK Code                             | IK10  |
| Note                                | A cover plate is required to seal the pedestal<br>A desk unit and desk unit cover plate are required for 2-part console assembly<br>A desk unit and console are required for 3-part console assembly. |
| IP protection category to IEC 60529 | IP 55   |
| Protection category NEMA            | NEMA 1<br>NEMA 12   |
| Basic material                      | Sheet steel   |
| Number of locks                     | 1   |
| Lock version                        | 3-point lock system   |
| Lock insert                         | 3 mm double-bit   |
| Lock                                | Lock version: 3-point lock system<br>Number of locks: 1<br>Lock insert: 3 mm double-bit   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 56 kg   |
| Gross weight                        | 57.125 kg   |
| Customs tariff number               | 94032080  |
| ETIM 9                              | EC000784  |
| ETIM 8                              | EC000784  |
| ECLASS 8.0                          | 27180504  |
| Product description                 | CX console system, pedestal, WxHxD: 1200x675x400 mm, sheet steel  |

# Approvals

---

Approvals

UL + C-UL (listed)

---

Explanations

Declaration of conformity