

Rittal – The System.

Faster – better – everywhere.



CS 9783.550

Outdoor Basic enclosures

State: 6/04/2026 (Source: rittal.com/au-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9783.550 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



Features

| | |
|---------------------|---|
| Model No. | CS 9783.550 |
| Product description | Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides. |
| Material | Aluminium AlMg3 |
| Surface finish | Powder-coated UV-resistant pure polyester |
| Colour | RAL 7035 |
| Supply includes | Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy |
| Dimensions | Width: 600 mm Height: 1,200 mm Depth: 400 mm |

Features

| | |
|------------|---|
| Dimensions | Overall height: 1,355 mm Rain canopy width: 650 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 512 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height base/plinth: 100 mm |
|------------|---|

| | |
|-----------------------|---------|
| Type rating to UL 50E | Type 3R |
|-----------------------|---------|

| | |
|-------------------------------------|-------|
| IP protection category to IEC 60529 | IP 55 |
|-------------------------------------|-------|

| | |
|---------|------|
| IK Code | IK10 |
|---------|------|

| | |
|----------------|-----------|
| Basic material | Aluminium |
|----------------|-----------|

| | |
|----------|----------|
| Packs of | 1 pc(s). |
|----------|----------|

| | |
|------------|----------|
| Net weight | 38.95 kg |
|------------|----------|

| | |
|--------------|-------|
| Gross weight | 41 kg |
|--------------|-------|

| | |
|-----------------------|----------|
| Customs tariff number | 94032080 |
|-----------------------|----------|

| | |
|--------|----------|
| ETIM 9 | EC000261 |
|--------|----------|

| | |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|
