

# Rittal – The System.

Faster – better – everywhere.



## DK 7111.210

## Cable routing bars, 482.6 mm (19") attachment

State: 20.03.2026 (Source: [rittal.com/bg-bg](https://www.rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7111.210 - Cable routing bars, 482.6 mm (19") attachment

For structured routing of entire cable bundles, 482.6 mm (19") attachment, connection comb.



## Features

|                         |                                                                                                                                                                                                                                                                                                |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.               | DK 7111.210                                                                                                                                                                                                                                                                                    |
| Design                  | Cranked attachment: For mounting angles and mounting frames.<br>Horizontal, U-based cable routing to the distributor level.                                                                                                                                                                    |
| Product description     | For structured routing of entire cable bundles, the cable bars may be secured to a variety of different positions inside the enclosure.                                                                                                                                                        |
| Applications            | For horizontal cable routing within the distributor level. Thanks to their open mounting holes, they can also be retrospectively slotted onto the 482.6 mm (19") system punchings of the mounting level at any time and secured with the existing mounting screws of the installed components. |
| Material                | Support: Sheet steel<br>Cable routing bars, connection combs: Plastic UL 94-V0                                                                                                                                                                                                                 |
| Colour                  | RAL 9005                                                                                                                                                                                                                                                                                       |
| Supply includes         | Cable routing bars<br>Connection combs                                                                                                                                                                                                                                                         |
| Number connection combs | 5                                                                                                                                                                                                                                                                                              |
| Note                    | Size of individual chambers (WxD) approx. 34 x 100 mm                                                                                                                                                                                                                                          |

# Features

|                       |           |
|-----------------------|-----------|
| Units                 | 1 U       |
| Packs of              | 10 pc(s). |
| Net weight            | 1,08 kg   |
| Gross weight          | 1,18 kg   |
| Customs tariff number | 73269098  |
| ETIM 9                | EC000322  |
| ECLASS 8.0            | 27400604  |

## Tender text

Cable bracket, cranked, 1U

Single cable bracket, cranked, for mounting rails or mounting frames, for feeding individual cable bunches or for extension of existing units through baying by means of connecting piece. For this the connecting piece is put between two bracket elements and thus connects the elements by forming an additional guide chamber between the bracket elements. The connecting pieces needed for baying are contained within the units. delivery scope. The single bracket has a height of approx one height unit (44.45 mm) and thus enables the U related cable feed of whole cable bunches.

Each individual cable bracket can be opened selectively and independently of the others and closed again by means of a turning catch. It thus enables straightforward structuring of the cabling and also flexible change to it.

Support element sheet steel, spray finished

Cable feed brackets, connecting pieces, turning catches, plastic.