

# Rittal – The System.

Faster – better – everywhere.



## SV 9345.015 Fuse holders

State: 14.05.2026 (Source: [rittal.com/bg-bg](http://rittal.com/bg-bg))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.015 - Fuse holders 31 A to 60 A

Fuse holders up to 60 A, 3-pole. Simple mounting on support rails or via OM component adaptors on busbars.

## Features

|                                    |  |
|------------------------------------|--|
| Model No.                          | SV 9345.015  |
| Design                             | For category J fuse type   |
| Material                           | Polyamide<br>Fire protection corresponding to UL 94-V0   |
| Colour                             | RAL 7035   |
| Connection for round conductor     | AWG 1 - 18   |
| Type of electrical connection      | Box terminal   |
| For fuse type (class)              | J  |
| Rated operating current max.       | 30 A   |
| Rated operating voltage            | 600 V, 3~  |
| Fuse standard                      | UL 248-8   |
| Note                               | For snap-on mounting on 35 mm (7.5 mm/15 mm high) support rails to DIN EN 60 715 or RiLine component adaptor combinations (OM adaptors/supports) |
| Test specification                 | UL 4248-1<br>UL 4248-4<br>UL 4248-8  |
| Dimensions                         | Width: 108 mm<br>Height: 115 mm  |
| Connection of round conductors     | 1.5 - 50 mm <sup>2</sup>   |
| To fit fuses                       | Diameter: 21 mm<br>Length: 57 mm   |
| Voltage range for indicator lights | 110 - 600 V  |
| Electrical ratings UL (SCCR)       | 200 kA - 600 V, Fuse Class J max. 30 A, JDDZ/7   |

## Features

---

|                               |  |
|-------------------------------|--|
| Number of poles               | 3-pole   |
| Round conductor cross-section | 1.5 - 50 mm <sup>2</sup>                             |
| Packs of                      | 2 pc(s).   |
| Net weight                    | 0,84 kg  |
| Gross weight                  | 0,966 kg   |
| Copper weight (kg per piece)  | 0,072  |
| Customs tariff number         | 85369095   |
| ETIM 9                        | EC001644   |
| ECLASS 8.0                    | 27400613   |
| Product description           | SV Fuseholder, Class J, 30 A, 600 V, 3-pole, (60 mm) |

---

## Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

---