

Rittal – The System.

Faster – better – everywhere.



PC 5366.050 PC enclosure system

State: 2026-07-09 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5366.050 - PC enclosure system

Secure accommodation of all PC components, from monitors, to PCs and keyboards. Extremely simple to use and modern design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access.



Features

Model No.	PC 5366.050
Version	with glazed door at the top, keyboard drawer and component shelf
Product description	Secure accommodation of all PC components, from monitors, to PCs and keyboards. For ultimate ease of operation in a contemporary design. Complete protection from humidity and dirt, temperature fluctuations and unauthorized access.
Material	Housing, door, rear door, mounting compartment, supports: carbon steel Handles, decorative trim panels: Plastic Door trim panels: Aluminum Viewing window: Single-pane safety glass
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
General color	RAL 7035
Color	Housing, door, decorative trim panels, supports: RAL 7035 Handle: RAL 7015 Monitor field, door center section: RAL 7015

Features

Supply includes	Housing, door, rear door Base Plates Glazed door, top Keyboard drawer Component shelf
Dimensions	Width: 600 mm Height: 1,600 mm Depth: 636 mm
Protection category IP to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Type rating according to UL 50E	Type 1 Type 12
Max. keyboard dimensions (WxHxD)	480 x 70 x 260 mm
Base material	Carbon steel
Packaging unit	1 pc(s).
Net weight	93.5 kg
Gross weight	95.8 kg
PCF/VE (cradle-to-gate)	386.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94032080
ETIM 9	EC002502
ECLASS 8.0	27180501
Product description	PC PC enclosure system, WHD: 600x1600x636 mm, Sheet steel, with glazed door at the top, folding keyboard, component shelf

Approvals

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Declaration of conformity Declaration of conformity UK
