

Rittal – The System.

Faster – better – everywhere.



CP 6212.060

Support Profile, Height-Adjustable

State: 2026-04-02 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6212.060 - Support Profile, Height-Adjustable for support arm systems

The new height-adjustable support section always provides the right view of the key parameters in human/machine interaction. The system can be fitted directly to the components of the CP 120 support arm system on the wall side, and to the CP 60 support arm system on the enclosure side without further adaption.



Features

Model No.	CP 6212.060
Product description	The new height-adjustable support profile, always provides the right view of the key parameters in human/machine interaction. On the wall side, the system can be fitted directly to the components of the CP 120 support arm system without any further adaptation, and on the enclosure side, either to support arm system CP 60 or CP 120, depending on the model.
Benefits	<ul style="list-style-type: none">Support arm holds in every positionAdditional fixing via clamping levers possiblePrecise adjustment to the trailing load through an adjusting screw on the front of the support profileAdjusting screw can be accessed without dismantling any componentsSafety through large cable troughs and cable guides at the swing pointsRemovable side panel for easy access to the cable routingTilting angle of the mounted housing is identical in every height positionCables with connectors such as DVI and VGA are also easily insertedBroad weight range from 4 to 60 kg with three systems. (Weight range applies to configured enclosure and vertical support section)

Features

Technical specifications	Cable trough: 36 x 11 mm (W x H), max. connector gland: 41 x 17 mm (W x H) Offers enhanced ergonomics through 600 mm (\pm 300 mm) adjustment range
Applications	For tall and short operators For sitting or standing workstations
Material	Hinge: Cast aluminum Concertina section: Plastic
Color	RAL 7035
Supply includes	Assembly components
Length	741 mm
Connection options enclosure	CP 60
Connection options wall / machine	CP 120
Note	In combination with support support section, height adjustable observe: When using an intermediate hinge, the height-adjustable support section should always be inserted in the closest horizontal position to the enclosure.
Dimensions	Length: 741 mm
Load	4 kg...30 kg
Note on Model No.:	Maximum cross-section for cable entry 41 x 17 mm Weight range applies to configured housing and vertical support section.
Packaging unit	1 pc(s).
Net weight	10.8 kg
Gross weight	11.8 kg
Customs tariff number	73269060
ETIM 9	EC000882
ECLASS 8.0	27400556
Product description	CP support section height-adjustable, CP 120/60, for weight range 4-30 kg