

**Rittal – The System.**

Faster – better – everywhere.



**VX 8640.005**

**Base/plinth corner piece with base/  
plinth trim panels, front and rear,  
100 mm**

State: 02/12/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8640.005 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.

## Features

Model No.	VX 8640.005
Product description	High-load capacity base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 base/plinth corner pieces, 100 mm high 4 corner covers 1 baying cover 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth
Dimensions	Height: 100 mm

# Features

---

To fit	Enclosure type: VX VX IT VX SE TS IT TX CableNet Width: = 1,000 mm
--------	---

---

Type rating to UL 50E	Type 1 Type 12
-----------------------	-------------------

---

Weight/pack	5.94 kg
-------------	---------

---

Packs of	2 pc(s).
----------	----------

---

Net weight	5.5
------------	-----

---

Gross weight	5.94
--------------	------

---

Customs tariff number	94039910
-----------------------	----------

---

EAN	4028177958784
-----	---------------

---

E-Number Sweden	E3465365
-----------------	----------

---

ETIM 9	EC000721
--------	----------

---

ETIM 8	EC000721
--------	----------

---

ECLASS 8.0	27182003
------------	----------

---

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------