

# Rittal – The System.

Faster – better – everywhere.



## VX 8617.120

# Punched section with mounting flange, 23 x 64 mm

State: 04/06/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.120 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



## Features

|                            |                                                                                                                                                                                                       |
|----------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                  | VX 8617.120                                                                                                                                                                                           |
| Product description        | For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.                                                        |
| Benefits                   | Simply locate into the system punchings and screw-fasten<br>System punchings on all four sides<br>With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material                   | Sheet steel                                                                                                                                                                                           |
| Surface finish             | Zinc-plated                                                                                                                                                                                           |
| Supply includes            | Assembly parts                                                                                                                                                                                        |
| VX installation options    | In enclosure depth 500 mm, on the inner mounting level                                                                                                                                                |
| VX SE installation options | In enclosure depth 500 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility                                                                                         |
| AX installation options    | In enclosure width/height 500 mm, in conjunction with rail for interior installation AX and base configuration rail for AX                                                                            |

# Features

|                                         |                                                                                                           |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------|
| AX stainless steel installation options | In enclosure width/height 500 mm, in conjunction with the base configuration rail                         |
| Installation options, AX plastic        | In enclosure width 500 mm, in conjunction with universal bracket                                          |
| CX installation options                 | In the pedestal, in the enclosure depth, 500 mm                                                           |
| VX base/plinth installation options     | In base/plinth width/depth 600 mm for mounting on the base/plinth corner pieces                           |
| To fit                                  | Enclosure type: VX<br>VX IT<br>VX SE<br>AX<br>AX plastic<br>Suitable for width or height or depth: 500 mm |
| To fit                                  | Base/plinth system VX                                                                                     |
| Packs of                                | 4 pc(s).                                                                                                  |
| Net weight                              | 1.6 kg                                                                                                    |
| Gross weight                            | 1.98 kg                                                                                                   |
| PCF per pack (cradle-to-gate)           | 10.8                                                                                                      |
| Customs tariff number                   | 73269098                                                                                                  |
| ETIM 9                                  | EC002620                                                                                                  |
| ECLASS 8.0                              | 27189234                                                                                                  |
| Product description                     | VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level, for W/H/D: 500 mm          |

# Approvals

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|