

# Rittal – The System.

Faster – better – everywhere.



## VX 8617.130

## Punched section with mounting flange, 23 x 64 mm

State: 01/09/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.130 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



## Features

|                            |   |
|----------------------------|---|
| Model No.                  | VX 8617.130   |
| Product description        | For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.  |
| Benefits                   | Simply locate into the system punchings and screw-fasten<br>System punchings on all four sides<br>With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material                   | Sheet steel   |
| Surface finish             | Zinc-plated   |
| Supply includes            | Assembly parts  |
| VX installation options    | In enclosure width/depth 600 mm, on the inner mounting level  |
| VX SE installation options | In enclosure width/depth 600 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility   |
| AX installation options    | In enclosure width/height 600 mm, in conjunction with rail for interior installation AX and base configuration rail for AX  |

# Features

|   |  |
|---|--|
| AX stainless steel installation options | In enclosure width/height 600 mm, in conjunction with the base configuration rail                                      |
| Installation options, AX plastic        | In enclosure width 600 mm, in conjunction with universal bracket   |
| PC installation options                 | In enclosure width 600 mm, in conjunction with adaptor rail for VX compatibility                                       |
| WI installation options                 | In enclosure width/depth 600 mm, in conjunction with adaptor rail for VX compatibility                                 |
| VX base/plinth installation options     | In base/plinth width/depth 600 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket |
| To fit                                  | Enclosure type: VX<br>VX IT<br>VX SE<br>PC<br>IW<br>AX<br>AX plastic<br>Suitable for width or height or depth: 600 mm  |
| To fit                                  | Base/plinth system VX  |
| Packs of                                | 4 pc(s).   |
| Net weight                              | 2.24   |
| Gross weight                            | 2.43   |
| Customs tariff number                   | 73269098   |
| EAN                                     | 4028177829138  |
| ETIM 9                                  | EC002620   |
| ECLASS 8.0                              | 27189234   |