


# Rittal – The System.

Faster – better – everywhere.



## VX 7993.126

## Bayed enclosure system VX25

State: 16.04.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 7993.126 - Bayed enclosure system VX25 BMW AG

## Group standard

Valid in all BMW AG component and car factories. VX25 enclosures with 200 mm high base/plinth, for TMO.

## Features

|                     |  |
|---------------------|--|
| Model No.           | VX 7993.126  |
| Product description | Valid in all BMW AG component and car factories. VX25 enclosures with 200 mm high base/plinth, for TMO.  |
| Material            | Enclosure frame: Sheet steel, 1.5 mm<br>Roof: Sheet steel, 1.5 mm<br>Door: Sheet steel, 2.0 mm<br>Rear panel: Sheet steel, 1.5 mm<br>Gland plates: Sheet steel, 1.5 mm<br>Mounting plate: Sheet steel, 3.0 mm  |
| Surface finish      | Enclosure frame: Dipcoat-primed<br>Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Mounting plate and gland plates: Zinc-plated   |
| Colour              | RAL 7035   |
| Supply includes     | Door(s) with fitted 180° hinges 8618.330<br>Door(s) with fitted comfort handle for profile half-cylinders 8618.250 including fitted adaptor kit for double-bit lock insert 7993.200<br>Base/plinth height: 200 mm, consisting of corner pieces and base/plinth components front and rear 8660.02X, height of base/plinth trim panels 2 x 100 mm at the front and 1 x 200 mm at the rear<br>With zinc-plated mounting plate, mounted in the rearmost position in the final raster hole<br>With LED system light 2500.220, 24 V at the front, with infeed 2500.410 and with fitted door-operated switch 2500.460 |
| Dimensions          | Width: 600 mm<br>Height: 2,000 mm<br>Depth: 600 mm   |

# Features

---

|                                   |                   |
|-----------------------------------|-------------------|
| Height including base/plinth      | 2.200 mm          |
| Dimensions mounting plate (W x H) | 499 mm x 1,896 mm |
| Number of doors                   | 1                 |
| Packs of                          | 1 pc(s).          |
| Customs tariff number             | 94032080          |

---