

Rittal – The System.

Faster – better – everywhere.



VX 7993.517

Bayed enclosure system VX25

State: 04.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 7993.517 - Bayed enclosure system VX25

Volkswagen-standard for plants in the USA

Group enclosure, including 200 mm base/plinth without mounting plate, for installing a wiring system. For use in accordance with the project-specific approved-material lists for the relevant brand.

Features

Model No.	VX 7993.517
Material	Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated
Colour	RAL 7035

Features

Supply includes	<p>Enclosure frame</p> <p>Door(s)</p> <p>Roof plate</p> <p>Rear panel</p> <p>Lock: 3 mm double-bit without mounting plate</p> <p>Base/plinth, 200 mm high, comprising: 4 sheet steel base/plinth corner pieces, front and rear with solid trim panel 8660.02X, with solid trim panels 8660.043 at the sides</p> <p>Potential equalisation of the roof, side panels and gland plates is achieved automatically during assembly via contact elements</p> <p>Door(s) earthed at the top with EMC earthing braid 2412.316 on the enclosure frame with threaded block</p> <p>Comfort handle 8618.240 with integral E1 lock, supplied without keys (supplied loose)</p> <p>2 base mounting plates 8660.100 (supplied loose)</p> <p>LED system light 2500.300, 100 – 240 V, 1~, 50 Hz / 60 Hz, without socket, fitted at the top front</p> <p>Solid sheet steel door, one-piece, r/h door hinge, 180° hinges</p> <p>Zinc-plated gland plates, three-part, with cut-out for cable entry and fitted brush strip</p>
Number of doors	2
Basic material	Sheet steel
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 600 mm</p>
Height including base/plinth	2.200 mm
Lock version	3-point lock system with VW E1 lock
Packs of	1 pc(s).
Net weight	113,6 kg
Gross weight	118,6 kg
Customs tariff number	94032080