


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.132 Wire Station WS 540

State: 6/09/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.132 - Wire Station WS 540

Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.



## Features

Model No.	AS 4051.132
Design	Wire Terminal Edition
Product description	Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.
Benefits	<ul style="list-style-type: none"><li>Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm</li><li>Multiplex worktop, washable and scratch-resistant</li><li>Ideal solution in conjunction with the length-cutting and crimping machines plus pre-assembled wires with the Wire Terminal</li><li>Integral scale for quick manual measurements</li><li>Prepared to accommodate a monitor for wire processing with Eplan Smart Wiring</li><li>Optionally expandable with shelves for wire boxes, wire reels and holders for tools and small parts</li><li>For flexible use in the workshop thanks to rubberised wheels</li><li>Drawer with shadow board prepared for tools</li></ul>

# Features

Supply includes	Wiring table with electrical height adjuster Connection cable, 7 m 7-way socket strip, with rocker switch 1 Wire Station WS 540 2 shelves 1 component support, left 1 monitor attachment 1 LED work light 4 mounting struts, vertical 4 adaptor brackets 1 mini-PC holder 1 magazine support 1 socket strip, 5-way 1 waste bin 1 wire pack holder, left 1 wire pack holder, right 1 wire coil holder, left 1 wire coil holder, right 1 wire guide strut, vertical
Assembly instruction	The vertical mounting struts, Model No. 4051.106, are required for accessories such as storage box holders, magazine supports etc.
Input voltage	230 V AC, 50 Hz
Working height	Working height (min.): 710 mm Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Applications	For use in conjunction with the Rittal Wire Terminal WT
Packs of	1 pc(s).
Net weight	173.8
Gross weight	242.3
Customs tariff number	84571090
EAN	4028177963641
ETIM 8	EC002778
ECLASS 8.0	21100208

# Approvals

---

Explanations

Declaration of conformity