

# Rittal – The System.

Faster – better – everywhere.



DK 7824.360

Sheet steel door, vertically divided,  
vented

State: 4/3/2026 (Source: [fin-en](#))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7824.360 - Sheet steel door, vertically divided, vented for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

## Features

|                                      |                                                                                                                                                                                                                                                                                                                                                                                                               |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                            | DK 7824.360                                                                                                                                                                                                                                                                                                                                                                                                   |
| Product description                  | With 130° hinges and locking rod, including comfort handle for profile half-cylinders with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced. The extensive door perforations additionally support climate control of the installed equipment. Perforated surface with air inlet openings > 78%. |
| Material                             | Sheet steel                                                                                                                                                                                                                                                                                                                                                                                                   |
| Supply includes                      | Assembly parts                                                                                                                                                                                                                                                                                                                                                                                                |
| IP protection category to IEC 60 529 | IP 20                                                                                                                                                                                                                                                                                                                                                                                                         |
| To fit                               | Enclosure type: DK-TS<br>Width: 600 mm<br>Height: 2,000 mm                                                                                                                                                                                                                                                                                                                                                    |
| Packs of                             | 1 pc(s).                                                                                                                                                                                                                                                                                                                                                                                                      |
| Net weight                           | 22.6 kg                                                                                                                                                                                                                                                                                                                                                                                                       |
| Gross weight                         | 23.2 kg                                                                                                                                                                                                                                                                                                                                                                                                       |
| Customs tariff number                | 94032080                                                                                                                                                                                                                                                                                                                                                                                                      |
| ECLASS 8.0                           | 27182204                                                                                                                                                                                                                                                                                                                                                                                                      |

# Tender text

Vertically divided vented sheet steel door,  
W x D = 600 x 2000

Sheet steel door with 130° hinges and assembly parts,  
locking rod including comfort handle for semi-cylinder  
with 3524 E security lock.

Material: Sheet steel, spray finished in RAL 7035  
Enclosure W x D: 600 mm x 2000 mm