

# Rittal – The System.

Faster – better – everywhere.



## CX 6702.000

## CX ベースユニット

State: 2026/07/11 (Source: [rittal.com/jp-ja](http://rittal.com/jp-ja))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CX 6702.000 - CX ベースユニット

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



## Features

品番	CX 6702.000
仕様	ベースユニット
材質	エンクロージャー：鋼板 1.5 mm ドア：鋼板製、2.0 mm、周囲に発泡ポリウレタンパッキンを塗布 マウンティングプレート：鋼板製、2.5 mm
表面	エンクロージャーとドア：電着浸漬下塗り、外側は静電粉体塗装、凹凸模様（テクスチャー）仕上げ マウンティングプレート：亜鉛めっき
塗装色	RAL 7035
同梱品	エンクロージャー、上部オープン フロントドアおよびフロント両開きドア、3点ロックシステム付き マウンティングプレート グランドプレート ロック：ダブルビットNo.5/3 mm

# Features

寸法：	幅: 1,200 mm 高さ: 675 mm 奥行: 400 mm
マウンティングプレートの寸法 (幅 x高さ)	1,120 mm x 625 mm
ドアの数	2
ドア開角度	130°
IKコード	IK10
注記：	ベースユニットを塞ぐためには、エンドプレート (カバー) が必要です 2 パーツ構成のコンソールには、デスクユニットとデスクユニット用のエンドプレート (カバー) が必要です 3 パーツ構成のコンソールには、デスクユニットとコンソールユニットが必要です
保護等級 IP (IEC 60 529 準拠)	IP 55
Protection category NEMA	NEMA 1 NEMA 12
基材	鋼板製
ロックの数	1
ロックの仕様	3点ロックシステム
ロックインサート	ダブルビット 3 mm
ロック	ロックの仕様: 3点ロックシステム ロックの数: 1 ロックインサート: ダブルビット 3 mm
1パック	1 個
純質量	56 kg

# Features

---

総質量	57.125 kg
関税率番号	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
製品説明	CX コンソールシステム、ベースユニット、幅x高さx奥行： 1200x675x400 mm、鋼板製

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	CE適合宣言書