

# Rittal – The System.

Faster – better – everywhere.



## IT 7100.110 OCP ORV3 rack

Состояние: 23.06.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# IT 7100.110 - OCP ORV3 rack

Open. Efficient. Scalable. Your IT infrastructure from Rittal with OCP ORV3, without busbar. The Open Compute Project (OCP) brings together leading companies with the goal of making open IT infrastructures more efficient, scalable and sustainable. Rittal is supporting this vision with its OCP-compliant Open Rack Version 3 (ORV3), which is now also available without an integral busbar.



## Функции

|              |  |
|--------------|--|
| Арт. №       | IT 7100.110  |
| Исполнение   | Open frame<br>without busbar   |
| Преимущества | Модульная система для индивидуальной возможности расширения<br>Flexible busbar selection, to suit the rack power density<br>Can be retrofitted without replacing the entire system<br>Modular configuration for AI and HPC applications<br>Hot-pluggable components in the rack simplify maintenance work<br>May be supplemented with a suitable direct liquid cooling solution<br>Quick integration thanks to integral castor modules, air baffle plates and levelling feet<br>Our range of accessories includes IT and power rails, 482.6 mm (19") adaptors, doors and side panels |
| Материал     | Листовая сталь   |
| Поверхность  | Грунтовка, снаружи порошковое покрытие   |
| Цвет         | RAL 9005   |

## Функции

|                         |   |
|-------------------------|---|
| Комплект поставки       | ОСР ORV3 rack<br>2 bracing struts, pre-assembled<br>Установленные ролики для высокой нагрузки<br>Levelling feet, pre-assembled<br>Уплотнение для соединения в линейку |
| Размер                  | Ширина: 600 мм<br>Высота: 2.286 мм<br>Глубина: 1.068 мм   |
| Единиц высоты           | 44 OU   |
| Нагрузочная способность | 14 000 N  |
| Основной материал       | Листовая сталь  |
| Упаковка                | 1 шт.   |
| Код ТНВЭД               | 94032080  |
| ETIM 8                  | EC002499  |
| ECLASS 8.0              | 27180207  |
| Описание продукта       | ОСР ORV3 rack without busbar, 44 OU, WHD: 600 x 2286 x 1068 mm, RAL 9005  |