

Rittal – The System.

Faster – better – everywhere.



RX 9360.612

RiLineX CB component adaptor

Состояние: 09.06.2026 (Источник: rittal.com/kz-ru)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.612 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the bottom.



Функции

| | |
|--|---|
| Арт. № | RX 9360.612 |
| Исполнение | universal |
| Преимущества | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Материал | Полиамид (PA 6) Негорючесть согласно UL 94 |
| Цвет | RAL 9005 RAL 35745 |
| Комплект поставки | 3 connection space covers |
| Степень защиты IP согл. МЭК 60 529 | IP 2XB |
| Номинальное импульсное напряжение Uimp | 8 кВ |

Функции

| | |
|---------------------------------------|---|
| Rated voltage | 690 V AC 600 V AC (UL) |
| Номинальное напряжение изоляции U_i | 1 000 В |
| Степень загрязнения | 3 |
| Количество полюсов | 3-пол. |
| Отвод проводов | снизу |
| Сечение | 15 мм ² 6 мм ² |
| Подходит для производителя (тип) | Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor. |
| Подходит для шинной системы | RiLineX RiLine60 |
| Fundamental frequency | 50...60 Гц |
| Влажность воздуха (без конденсата) | 10...90 % |
| Подходит для шин | 15 x 5/10 20 x 5/10 30 x 5/10 |
| Диапазон рабочих температур | -25 °C...55 °C |
| Диапазон температур хранения | -25 °C...75 °C |
| Размер | Ширина: 108,7 мм Высота: 251,4 мм Глубина: 62,8 мм |
| Упаковка | 1 шт. |
| Вес нетто | 1,472 kg |
| Gross weight | 1,474 kg |
| Доля меди (кг / штук) | 0,608 |
| PCF per pack (cradle-to-gate) | 9,96 |
| Код ТНВЭД | 85369095 |

Функции

ETIM 9

EC001531

Описание продукта

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.

Одобрения

Одобрения

UL + C-UL (listed)

Объяснения

Декларация о соответствии
PCF-declaration