


# Rittal – The System.

Faster – better – everywhere.



## RX 9362.210

## RiLineX NH fuse-switch disconnecter

Состояние: 22.05.2026 (Источник: [rittal.com/kz-ru](http://rittal.com/kz-ru))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9362.210 - RiLineX NH fuse-switch disconnecter

RiLineX NH fuse-switch disconnecter in size 2 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnecters have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required.



## Функции

Арт. №	RX 9362.210
Исполнение	For 60 mm busbar systems
Преимущества	Cover: can be locked and prepared for a lead seal Voltage test through separate opening Tool-free changeover of the cable outlet Park position for simpler maintenance work All variants also available with electronic fuse monitoring
Материал	Полиамид (PA 6) Негорючесть согласно UL 94 Контактные поверхности: посеребренная твердая медь
Цвет	RAL 9005 RAL 35745
Для шинных систем с межцентровым расстоянием	60 mm
Отвод проводов	сверху/снизу
Тип подключения (электрического)	Винт M10
Плавкие вставки	NH 2

## Функции

Номинальное рабочее напряжение	690 В AC
Для размера NH	2
Test specification	МЭК/DIN EN 60 947-3 DIN EN 60 269-2 (плавкие вставки)
Размер	Ширина: 208,5 мм Высота: 298,6 мм Глубина: 134,6 мм
Диапазон рабочих температур	-5 °C...35 °C
Диапазон температур хранения	-25 °C...70 °C
Подходит для шин	15 x 5/10 20 x 5/10 30 x 5/10
Подходит для шинной системы	RiLineX RiLine60
Количество полюсов	3-пол.
Степень загрязнения	3
Степень защиты IP согл. МЭК 60 529	IP 2XB
Fire load	46,16 MJ/m <sup>2</sup>
Тепловыделение макс.	98 Вт
Упаковка	1 шт.
Вес нетто	3,87 kg
Gross weight	3,942 kg
Доля меди (кг / штук)	1,75
PCF per pack (cradle-to-gate)	26,35
Код ТНВЭД	85369095
ETIM 9	EC001040

## Функции

---

Описание продукта

RiLineX NH fuse-switch disconnecter in size 2 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required.

## Одобрения

---

Одобрения

CQC-CCC

Объяснения

Декларация о соответствии  
PCF-declaration