

# Rittal – The System.

Faster – better – everywhere.



## TS 4696.000

### Support strip

State: 2026.1.31 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 4696.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



## Features

Model No.	TS 4696.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm pitch pattern
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	540 mm
VX installation options	In enclosure width/depth 600 mm
VX SE installation options	In enclosure width/depth 600 mm, on the outer mounting level
AX installation options	In door width 600 mm, with cam lock In door width 600 mm, with 3-point lock system, in the hinged door
AX stainless steel installation options	In door width 600 mm, in hinged door, in conjunction with the perforated door strip
PC installation options	In enclosure width 600 mm, on the outer mounting level
WI installation options	In enclosure width/depth 600 mm, on the outer mounting level
TS installation options	In enclosure width/depth 600 mm, on the outer mounting level

# Features

AE installation options	In enclosure width/height 600 mm, in conjunction with rail for interior installation AE
TP installation options	In consoles for 3-part assembly, at the height of the enclosure cover, in conjunction with rail for interior installation for TP, compact enclosure HD
VX base/plinth installation options	In base/plinth width/depth 600 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket
To fit	Enclosure type: VX TS VX SE TP PC IW AX AE Width/depth: 600 mm
To fit	Base/plinth system VX
Packs of	20 pc(s).
Net weight	5.22
Gross weight	5.54
PCF per pack (cradle-to-gate)	21.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177108158
E-Number Sweden	E3465252
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261