


Rittal – The System.

Faster – better – everywhere.



CP 6212.065

Support section, height-adjustable

State: 2026.6.2 (Source: rittal.com/lt-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6212.065 - Support section, height-adjustable for support arm systems

The new height-adjustable support section ensures that you always have a good view of the key parameters in human/machine interaction. The system can be fitted directly to the components in the CP 120 support arm system without any further adaptation on the wall side, and on the enclosure side on support arm system CP 60.



Features

Model No.	CP 6212.065
Product description	The new height-adjustable support section ensures that you always have a good view of the key parameters in human/machine interaction. The system can be fitted directly to the components in the CP 120 support arm system without any further adaptation on the wall side, and on the enclosure side on support arm system CP 60 or CP 120 depending on the model.
Benefits	<ul style="list-style-type: none">Support arm holds securely in any positionPrecise coordination to the suspended load via an adjusting screw at the front of the support sectionAdjusting screw can be accessed without dismantling any componentsLarge cable tray and cable cable routing at the rotation points for safetyRemovable cover for simple cable entryTilting angle of the mounted enclosure is identical in every height positionCables with connectors such as DVI, VGA are easily insertedBroad weight range from 4 to 60 kg with three systems. (Weight range applies to configured enclosure and vertical support section.)

Features

Technical specifications	Cable tray: 36 x 11 mm (W x H), max. connector gland: 41 x 17 mm (W x H) More ergonomic with an adjustment range of 990 mm (± 495 mm)
Applications	For tall and short operators For seated and standing work
Material	Joint parts: Cast aluminium Concertina section: Plastic
General colour	RAL 7035
Colour	RAL 7035
Supply includes	Assembly parts
Length	1,100 mm
Connection options enclosure	CP 60
Connection options wall / machine	CP 120
Note	In combination with support support section, height adjustable observe: When using an intermediate hinge, the height-adjustable support section should always be inserted in the closest horizontal position to the enclosure.
Dimensions	Length: 1,100 mm
Load capacity	4 kg...15 kg
Note on Model No.	Maximum cross-section for cable entry 41 x 17 mm Weight range applies to configured enclosure and vertical support section.
Packs of	1 pc(s).
Net weight	15.2 kg
Gross weight	16 kg
Customs tariff number	73269098
ETIM 9	EC000882
ECLASS 8.0	27400556
Product description	CP support section, height-adjustable, for CP 120/60, length 1050 mm