

# Rittal – The System.

Faster – better – everywhere.



## CP 6315.600

# Command panels with handle strips

State: 2026.6.4 (Source: [rittal.com/lt-en](http://rittal.com/lt-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6315.600 - Command panels with handle strips

Operating housings with modern sheet steel handle strips, with support arm cut-out Ø 130 mm to fit support arm system CP 60 / 120 / 180, service access optionally from the front or rear, aluminium front panel easily removable for machining, protection category IP 55.



## Features

|                 |   |
|-----------------|---|
| Model No.       | CP 6315.600   |
| Material        | Enclosure and door: Sheet steel<br>Handle strips: Aluminium<br>Front panel: Aluminium<br>Cover caps: Plastic  |
| Surface finish  | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Handle strip: Natural anodised<br>Front panel: Natural anodised   |
| Colour          | Enclosure and door: RAL 7035<br>Handle strip: Natural anodised<br>Front panel: Natural anodised<br>Cover caps: similar to RAL 7024  |
| Supply includes | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm<br>Front with maximum cut-out, covered with easily machinable 3 mm aluminium front panel<br>Side handle strips and cover caps<br>Cam lock with 3 mm double-bit insert<br>Integral interior installation bracket with TS system punchings |

# Features

|                                     |   |
|-------------------------------------|---|
| Dimensions                          | Width: 600 mm<br>Height: 600 mm<br>Depth: 210 mm  |
| IP protection category to IEC 60529 | IP 55   |
| Design                              | Servicing access from the front   |
| Note                                | The support arm connection and door hinge may be swapped over by rotating the enclosure<br>Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out<br>Lock systems for servicing access from the front: 41 mm lock inserts, type C, lock cylinder, plastic handles and T handles, type C |
| Basic material                      | Aluminium   |
| Note on Model No.                   | Matching mounting panel 5050.442 with dispatch bag 5050.507   |
| Lock                                | Lock version: Crescent-shaped cam<br>Number of locks: 2<br>Lock insert: 3 mm double-bit   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 17.2 kg   |
| Gross weight                        | 17.59 kg  |
| Customs tariff number               | 94032080  |
| ECLASS 8.0                          | 27180505  |
| Product description                 | CP Operating housing with handle strips, WHD: 600x600x210 mm, Sheet steel, handle strips made of aluminum, Servicing access from the front  |

# Approvals

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|