


Rittal – The System.

Faster – better – everywhere.



VX 8617.130

Punched section with mounting flange, 23 x 64 mm

State: 2026.2.23 (Source: [ittal.com/lt-en](https://www.ittal.com/lt-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8617.130 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



Features

| | |
|----------------------------|---|
| Model No. | VX 8617.130 |
| Product description | For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures. |
| Benefits | Simply locate into the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| VX installation options | In enclosure width/depth 600 mm, on the inner mounting level |
| VX SE installation options | In enclosure width/depth 600 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility |
| AX installation options | In enclosure width/height 600 mm, in conjunction with rail for interior installation AX and base configuration rail for AX |

Features

| | |
|---|--|
| AX stainless steel installation options | In enclosure width/height 600 mm, in conjunction with the base configuration rail |
| Installation options, AX plastic | In enclosure width 600 mm, in conjunction with universal bracket |
| PC installation options | In enclosure width 600 mm, in conjunction with adaptor rail for VX compatibility |
| WI installation options | In enclosure width/depth 600 mm, in conjunction with adaptor rail for VX compatibility |
| VX base/plinth installation options | In base/plinth width/depth 600 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket |
| To fit | Enclosure type: VX VX IT VX SE PC IW AX AX plastic Suitable for width or height or depth: 600 mm |
| To fit | Base/plinth system VX |
| Packs of | 4 pc(s). |
| Net weight | 2.24 kg |
| Gross weight | 2.43 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level, for W/H/D: 600 mm |