Rittal - The System.

Faster - better - everywhere.





SV 9340.910 OM adaptors

State: 18/11/2025 (Source: rittal.com/nz-en)



SV 9340.910 - OM adaptors with plug-in cable outlet



Features

Model No.	SV 9340.910
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 7035
Supply includes	Connector with connection facility for 3 main contacts (1.5 – 4 mm^2)
Rated current max.	25 A
Rated operating voltage	690 V, 3~
For bar systems with centre-to- centre spacing	60 mm
Support rail type	Support frame, 1 x TS 45D, 1 x TS 45D-V
Number of poles	3-pole
Connector outlet	Connector with connection facility for 3 main contacts (1.5 – 4 mm²)
Dimensions	Width: 45 mm Height: 208 mm
Connection of round conductors	1.5 - 4 mm²
Support rails Qty/height	2 / 10 mm
To fit busbars	Height: 5, 10 mm
Support frame (W x H)	45 mm x 170 mm

© Rittal 2025

Features

Packs of 1 pc(s). Net weight 0.201 Gross weight 0.289 Copper weight (kg per piece) 0.025 Customs tariff number 85369095 EAN 4028177555464 ETIM 9 EC001531 ETIM 8 EC001531 ECLASS 8.0 27370304		
Gross weight 0.289 Copper weight (kg per piece) 0.025 Customs tariff number 85369095 EAN 4028177555464 ETIM 9 EC001531 ETIM 8 EC001531	Packs of	1 pc(s).
Copper weight (kg per piece) 0.025 Customs tariff number 85369095 EAN 4028177555464 ETIM 9 EC001531 ETIM 8 EC001531	Net weight	0.201
Customs tariff number 85369095 EAN 4028177555464 ETIM 9 EC001531 ETIM 8 EC001531	Gross weight	0.289
EAN 4028177555464 ETIM 9 EC001531 ETIM 8 EC001531	Copper weight (kg per piece)	0.025
ETIM 9 EC001531 ETIM 8 EC001531	Customs tariff number	85369095
ETIM 8 EC001531	EAN	4028177555464
	ETIM 9	EC001531
ECLASS 8.0 27370304	ETIM 8	EC001531
	ECLASS 8.0	27370304

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3

Tender text

OM adaptor 25 A

OM adaptor 25 A premium adaptor 3-pole

for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Construction width: 45 mm

Length: 208 mm

Support frame: 45 x 170 mm

Support frame support: -

PinBlock: -

Connector outlet: with connection facility

for 3 main contacts

Support rail: -

System:

Rittal RiLine60

© Rittal 2025 4