

Rittal – The System.

Faster – better – everywhere.



TS 4696.000 Support strip

State: 31/08/2025 (Source: [rittal.com/ro-ro](https://www.rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4696.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

| | |
|---|--|
| Model No. | TS 4696.000 |
| Product description | For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment. |
| Technical specifications | 4.5 mm diameter hole on a 25 mm pitch pattern |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Length | 540 mm |
| VX installation options | In enclosure width/depth 600 mm |
| VX SE installation options | In enclosure width/depth 600 mm, on the outer mounting level |
| AX installation options | In door width 600 mm, with cam lock In door width 600 mm, with 3-point lock system, in the hinged door |
| AX stainless steel installation options | In door width 600 mm, in hinged door, in conjunction with the perforated door strip |
| PC installation options | In enclosure width 600 mm, on the outer mounting level |
| WI installation options | In enclosure width/depth 600 mm, on the outer mounting level |
| TS installation options | In enclosure width/depth 600 mm, on the outer mounting level |

Features

| | |
|-------------------------------------|--|
| AE installation options | In enclosure width/height 600 mm, in conjunction with rail for interior installation AE |
| TP installation options | In consoles for 3-part assembly, at the height of the enclosure cover, in conjunction with rail for interior installation for TP, compact enclosure HD |
| VX base/plinth installation options | In base/plinth width/depth 600 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket |
| To fit | Enclosure type: VX TS VX SE TP PC IW AX AE To fit width/depth: 600 mm |
| To fit | Base/plinth system VX |
| Packs of | 20 pc(s). |
| Net weight | 5.22 |
| Gross weight | 5.54 |
| PCF per pack (cradle-to-gate) | 21.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177108158 |
| E-Number Sweden | E3465252 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |