

# Rittal – The System.

Faster – better – everywhere.



## DK 5302.010 Air baffle plate

State: 07/05/2026 (Source: [rittal.com/ro-ro](http://rittal.com/ro-ro))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5302.010 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, standard

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



## Features

|                 |  |
|-----------------|--|
| Model No.       | DK 5302.010  |
| Benefits        | To selectively boost the energy efficiency of your climate control system<br>Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level.  |
| Applications    | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.   |
| Material        | Sheet steel<br>Brush strip: Plastic, UL 94-HB<br>Brush strip fibres: Plastic PA6, halogen-free<br>Brush strip mounting body: Plastic PVC, contains halogen<br>Blanking panel: Plastic, fire protection: self-extinguishing to UL 94 HB, halogen-free |
| Surface finish  | Spray-finished   |
| Colour          | RAL 9005   |
| Supply includes | 2 vertical trim panels<br>2 horizontal trim panels<br>4 brush strips<br>4 cellular PU foam pieces<br>Assembly parts  |

# Features

|                       |   |
|-----------------------|---|
| Assembly instruction  | <p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning. The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p> |
| To fit                | <p>Width: = 600 mm<br/>Height: = 1,200 mm</p>   |
| Packs of              | 1 pc(s).  |
| Net weight            | 0,001 kg  |
| Gross weight          | 0,001 kg  |
| Customs tariff number | 56090000  |
| ETIM 9                | EC000331  |
| ECLASS 8.0            | 27189272  |
| Product description   | <p>Air baffle plate, for VX IT 19" mounting angles, standard, to separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. WxH: 600x1200 mm, RAL 9005</p>   |