

# Rittal – The System.

Faster – better – everywhere.



## SM 2384.030 Switch housings

State: 10/07/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SM 2384.030 - Switch housings Stainless steel

Switch housing made from stainless steel 1.4301 (AISI 304) with switch cut-outs, diameter: 22.5 mm. Protection category IP 66.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SM 2384.030   |
| Material                          | Enclosure: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish                    | Enclosure and cover: Brushed, grain 240   |
| Supply includes                   | Enclosure with cover<br>Quick-release fastener including plastic bushes   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |
| Dimensions                        | Width: 220 mm<br>Height: 100 mm<br>Depth: 90 mm   |
| Material thickness - cover        | 1,25 mm   |
| Material thickness - enclosure    | 1,25 mm   |
| Pitch pattern                     | 60 mm   |
| Cut-outs (quantity x diameter)    | 3 x 22.5 mm   |
| Lock                              | Lock version: Quick-release fastener including plastic bushes<br>Number of locks: 4                                   |
| Cable entry (quantity x diameter) | 3   |
| No. of metric knockouts           | 3   |
| Basic material                    | Stainless steel 1.4301 (AISI 304)   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 1,1 kg  |

# Features

---

|                               |  |
|-------------------------------|--|
| Gross weight                  | 1,226 kg   |
| PCF per pack (cradle-to-gate) | 4.46   |
| Customs tariff number         | 84879090   |
| ETIM 9                        | EC000261   |
| ETIM 8                        | EC000261   |
| ECLASS 8.0                    | 27180101   |
| Product description           | SM Switch housing, WHD: 220x100x90 mm, Stainless steel 1.4301, without mounting plate, 3 switch cut-outs |

# Approvals

---

|              |  |
|--------------|--|
| Explanations | Declaration of conformity<br>Declaration of conformity UK<br>PCF-declaration |
|--------------|--|