

**Rittal – The System.**

Faster – better – everywhere.



**VX 8619.700**

**Punched section with mounting  
flange, 14 x 39 mm**

State: 12/04/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8619.700 - Punched section with mounting flange, 14 x 39 mm for VX, VX SE, PC, IW, AX

For securing cable ducts, cable conduit holders, equipment installed on the door, etc.



## Features

|   |   |
|---|---|
| Model No.                               | VX 8619.700   |
| Product description                     | For attaching cable ducts, cable conduit holders, equipment installed on the door, etc.                         |
| Material                                | Sheet steel   |
| Surface finish                          | Zinc-plated   |
| Supply includes                         | Assembly parts  |
| Distance between fixing points          | 275 mm  |
| To fit door width                       | 400 mm  |
| VX installation options                 | In door width 400 mm  |
| AX installation options                 | In enclosure width 300 mm and in enclosure height 400 mm, in conjunction with rail for interior installation AX |
| AX stainless steel installation options | In enclosure width 300 mm   |
| Installation options, AX plastic        | In door width 400 mm  |
| Installation options for 3-part AX      | In enclosure depth 473 mm   |

# Features

|                         |   |
|-------------------------|---|
| CX installation options | In the pedestal, in the enclosure depth, 400 mm<br>In one-piece console pedestal, in enclosure depth 400 mm   |
| Assembly instruction    | For installation in AX sheet steel, only in conjunction with rail for interior installation AX  |
| Note                    | For installing your own components on the punched section with mounting flange, metal screws or self-tapping M5 screws are required                                 |
| To fit                  | Enclosure type: VX<br>AX<br>AX plastic<br>AX wall-mounted enclosure, 3-part<br>CX one-piece console<br>CX pedestal<br>Suitable for width or height or depth: 400 mm |
| Packs of                | 4 pc(s).  |
| Net weight              | 0,68 kg   |
| Gross weight            | 0,686 kg  |
| Customs tariff number   | 73269098  |
| ETIM 9                  | EC002620  |
| ECLASS 8.0              | 27189234  |
| Product description     | VX Punched section, with mounting flange 14 x 39 mm, for door width: 400 mm   |

# Approvals

|              |                 |
|--------------|-----------------|
| Explanations | PCF-declaration |
|--------------|-----------------|