

**Rittal – The System.**

Faster – better – everywhere.



**SV 9345.600**

**Circuit-breaker component adaptor**

State: 03/07/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9345.600 - Circuit-breaker component adaptor 3-pole

Circuit-breaker adaptor for universal, simplified assembly of circuit-breakers.



## Features

|   |   |
|---|---|
| Model No.                                     | SV 9345.600   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour  | RAL 7035  |
| Supply includes                               | Connection straps<br>Sliding blocks   |
| Rated current max.                            | 250 A   |
| Rated operating voltage                       | 690 V, 3~   |
| Note  | Cable outlet: Switch outlet or as outgoing cable from the switchgear<br>The technical data may vary for UL applications |
| Electrical ratings UL (SCCR)                  | 65 kA - 480 V, circuit breaker max. 250 A, DIVQ/7   |
| Cable outlet                                  | Top   |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Number of poles                               | 3-pole  |
| Dimensions                                    | Width: 105 mm<br>Height: 240 mm   |
| To fit busbars                                | Height: 5, 10 mm  |

# Features

---

|                              |  |
|------------------------------|--|
| To fit manufacturer (model)  | ABB (S3, T3, T4/320 A, T3 UL, T4 UL, XT3, XT4)<br>Allen Bradley (140U-J)<br>Eaton (NZM2, NZM2 UL, BZM B2)<br>GE (FE160, FE250, FD160)<br>Legrand (DPX 250)<br>Mitsubishi (NF125-SGW/HGW, NF160-SGW/HGW)<br>OEZ (BD250N, BD250S)<br>Schneider Electric (NS(X)100, NS(X)160, NS(X)250, GV7, NSF150, NSF250)<br>Schrack (MC2)<br>Siemens (VL150(X) UL, VL160(X), VL250, VL250 UL, 3RV10 63, 3RV13 63, 3RV13 64, 3VT2, 3VA12/20/21/22, 3VA52/61/62)<br>Terasaki (H125, L125, H160, L160, S160, E250, H250, L250) |
| Approvals                    | UL   |
| Packs of                     | 1 pc(s).   |
| Net weight                   | 1,426 kg   |
| Gross weight                 | 1,509 kg   |
| Copper weight (kg per piece) | 0,77   |
| Customs tariff number        | 85369095   |
| ETIM 9                       | EC001531   |
| ECLASS 8.0                   | 27370304   |
| Product description          | SV Circuit-breaker component adaptor, 250 A, 690 V, 3-pole, cable outlet top, with connection straps   |

# Approvals

---

|           |   |
|-----------|---|
| Approvals | ABS<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
|-----------|---|

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|