

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.103 RiLineX baying set

State: 21/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.103 - RiLineX baying set for basic module

RiLineX baying set, 3-pole, short version, including contact hazard protection cover. Used for baying two boards in a compact arrangement. Ideal for space-saving baying within an enclosure. The set is supplied without busbar connectors (9365003). These are available as accessories.



## Features

Model No.	RX 9360.103
Benefits	Scalable system lengths with basic modules Simple assembly Scalable rated currents thanks to variable busbar cross-sections Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Extensive range of system accessories
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 35745
Supply includes	Board end element, left and right Board module cover Board module base plate Assembly parts
Number of poles	3-pole
To fit Model No.	9365.003 9360.110 9360.120 9360.150

# Features

---

Dimensions	Height: 240 mm Depth: 77 mm
IP protection category to IEC 60529	IP 2XB
Packs of	2 pc(s).
Net weight	1,5 kg
Gross weight	1,752 kg
PCF per pack (cradle-to-gate)	10.18
Customs tariff number	85369010
ETIM 9	EC002270
Product description	RiLineX baying set, 3-pole, short version, including contact hazard protection cover. Used for baying two boards in a compact arrangement. Ideal for space-saving baying within an enclosure. Supply includes one end element left and right plus one base plate, a cover and assembly parts. The set is supplied without busbar connectors. These are available separately.

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

# Tender text

RiLineX Anreih-Set für Basismodul (kurz)

RiLineX baying set, short version, including contact hazard protection cover. Used for baying two boards in a compact arrangement. The set is supplied without busbar connectors (9365003).

For voltages up to 1000 V AC and 1500 V DC.

Tested short-circuit resistance up to 65 kA.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current max.: 550/800 A

Dimensions: 105 mm x 246 mm x 49,2 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360103