

# Rittal – The System.

Faster – better – everywhere.



## BG 1584.010 Bus-skåp BG

State: 2026-04-18 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# BG 1584.010 - Bus-skåp BG Rostfritt stål

Bus-skåp av rostfritt stål 1.4301, (AISI 304), inkl. 180°-gångjärn. Kapslingsklass IP 66.

## Features

|                                    |  |
|------------------------------------|--|
| Art. nr.                           | BG 1584.010  |
| Material                           | Skåp: Rostfritt stål 1,4301 (AISI 304)<br>Lock: Rostfritt stål 1.4301 (AISI 304), omgivande inskummad PU-tätning<br>180°-gångjärn: zinkjutgods |
| Ytbehandling                       | Skåp och lock: Streckslipat, korn 240<br>180°-gångjärn: kromade  |
| Leveransens omfattning             | Skåp med lock<br>180°-gångjärn (2 stycken)<br>Profilskena TH 35/7,5<br>Snabbkoppling inkl. plasthylsor   |
| Protection category NEMA           | NEMA 4X  |
| Kapslingsklass IP enligt EN 60 529 | IP 66  |
| Dimension                          | Bredd: 300 mm<br>Höjd: 300 mm<br>Djup: 80 mm   |
| Materialtjocklek låda              | 1,5 mm   |
| Materialtjocklek dörr              | 1,25 mm  |
| Position dörrupphängning           | höger/vänster  |
| Antal profilskenor                 | 1  |
| Lås                                | Utförande för lås: Snabbkoppling inkl. plasthylsor<br>Antal lås: 2   |
| Grundmaterial                      | Rostfritt stål 1.4301 (AISI 304)   |
| Förpackningsenhet                  | 1 st.  |
| Nettovikt                          | 3,1 kg   |
| Bruttovikt                         | 3,44 kg  |

# Features

---

|                    |  |
|--------------------|--|
| Tullvarukod        | 94032080   |
| ETIM 9             | EC000261   |
| ETIM 8             | EC000261   |
| ECLASS 8.0         | 27180101   |
| Produktbeskrivning | BG Busskåp, BHD: 300 x 300 x 80 mm, rostfritt stål 1.4301, utan montageplåt, med lock, profilskena |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)                                  |
| Explanations | Konformitetsförklaring<br>Konformitetsförklaring UK |