


# Rittal – The System.

Faster – better – everywhere.



## VX 8104.245

# Side panel, screw-fastened, sheet steel

State: 14/04/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8104.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.

## Features

|                                     |                                                                                                                                                                                                                                                                                                                                                                             |
|-------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                           | VX 8104.245                                                                                                                                                                                                                                                                                                                                                                 |
| Benefits                            | Time-saving assembly thanks to clip-in side panel holder<br>Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside<br>Easy positioning in the height and depth with the location aid<br>One-person assembly<br>Earthing bolts with large, paint-free contact surface for optimum contact |
| Material                            | Sheet steel, 1.5 mm                                                                                                                                                                                                                                                                                                                                                         |
| Surface finish                      | Dipcoat-primed, powder-coated on the outside                                                                                                                                                                                                                                                                                                                                |
| Colour                              | RAL 7035                                                                                                                                                                                                                                                                                                                                                                    |
| Supply includes                     | Assembly parts                                                                                                                                                                                                                                                                                                                                                              |
| To fit                              | Enclosure type: VX<br>Height: = 2,000 mm<br>Depth: = 400 mm                                                                                                                                                                                                                                                                                                                 |
| IP protection category to IEC 60529 | IP 55                                                                                                                                                                                                                                                                                                                                                                       |
| Type rating to UL 50E               | Type 1<br>Type 12                                                                                                                                                                                                                                                                                                                                                           |
| Basic material                      | Sheet steel                                                                                                                                                                                                                                                                                                                                                                 |
| Packs of                            | 2 pc(s).                                                                                                                                                                                                                                                                                                                                                                    |
| Net weight                          | 19.06 kg                                                                                                                                                                                                                                                                                                                                                                    |
| Gross weight                        | 19.4 kg                                                                                                                                                                                                                                                                                                                                                                     |
| PCF per pack (cradle-to-gate)       | 73.9 kg CO2 eq (Cat B)                                                                                                                                                                                                                                                                                                                                                      |

## Features

---

|                       |                                                                                                                |
|-----------------------|----------------------------------------------------------------------------------------------------------------|
| Note on PCF category  | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910                                                                                                       |
| ETIM 9                | EC002524                                                                                                       |
| ECLASS 8.0            | 27182101                                                                                                       |
| Product description   | VX Side panel, screw-fastened, for HD: 2000x400 mm, sheet steel                                                |

## Approvals

---

|              |                    |
|--------------|--------------------|
| Approvals    | UL + C-UL (listed) |
| Explanations | PCF-declaration    |