

# Rittal – The System.

Faster – better – everywhere.



## VX 8640.000

Base/plinth corner piece with base/  
plinth trim panels, front and rear,  
100 mm

State: 30/05/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8640.000 - Base/plinth corner piece with base/plinth trim panels, front and rear, 100 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Heavy-duty base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover.

## Features

|                     |   |
|---------------------|---|
| Model No.           | VX 8640.000   |
| Product description | High-load capacity base/plinth corner pieces with moulded self-positioning to the enclosure, may be used with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point, may be concealed with a plastic corner and baying cover. |
| Material            | Base/plinth corner piece: Sheet steel<br>Base/plinth trim panel front/rear: Sheet steel<br>Corner and baying cover: Plastic   |
| Colour              | RAL 9005  |
| Supply includes     | 4 base/plinth corner pieces, 100 mm high<br>4 corner covers<br>1 baying cover<br>2 base/plinth trim panels, front/rear, 100 mm high<br>Assembly parts   |
| Note                | Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth   |
| Dimensions          | Height: 100 mm  |

# Features

---

|                       |   |
|-----------------------|---|
| To fit                | Enclosure type: VX<br>VX IT<br>VX SE<br>TS IT<br>TX CableNet<br>Width: = 300 mm                                 |
| Type rating to UL 50E | Type 1<br>Type 12   |
| Weight/pack           | 3.72 kg   |
| Packs of              | 2 pc(s).  |
| Net weight            | 3.2 kg  |
| Customs tariff number | 94039910  |
| ETIM 9                | EC000721  |
| ETIM 8                | EC000721  |
| ECLASS 8.0            | 27182003  |
| Product description   | VX Base/plinth corner piece, with base/plinth trim panel, front and rear, H: 100 mm, for W: 300 mm, sheet steel |

---

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|