

# Rittal – The System.

Faster – better – everywhere.



## AE 1037.500

## Kompaktna ohišja AE

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1037.500 - Kompaktna ohišja AE

Enclosure with door of sheet steel, spray-finished with mounting plate and gland plate in the base

## Features

|                                    |  |
|------------------------------------|--|
| Št. Modela                         | AE 1037.500  |
| Material                           | Ohišje: jeklena pločevina<br>Vrata: jeklena pločevina, penasto PU tesnilo po celotnem obodu  |
| Površinska obdelava                | Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva<br>Montažna plošča: pocinkana  |
| Barva                              | RAL 7035   |
| Obseg dobave                       | Ohišje z vrati na tečajih, popolnoma zaprto<br>Plošča(e) z uvodnicami v podnožju ohišja<br>Montažna plošča<br>Ključavnica: 3 mm dvojna ključavnica |
| Razred zaščite NEMA                | NEMA 4   |
| Razred zaščite po IEC 60 529       | IP 66  |
| IK koda                            | IK08   |
| Mere                               | Širina: 400 mm<br>Višina: 800 mm<br>Globina: 300 mm  |
| Debelina materiala - vrata         | 2 mm   |
| Debelina materiala - ohišje        | 1,5 mm   |
| Debelina materiala montažne plošče | 3 mm   |
| Mere montažne plošče (Š x V)       | 349 mm x 770 mm  |
| Število vrat                       | 1  |
| Zamenljiv tečaj vrat               | Yes  |
| Število ključavnic                 | 2  |

# Features

---

|                             |  |
|-----------------------------|--|
| Zaklepanje                  | Različica ključavnice: Ključavnica<br>Število ključavnic: 2<br>Vložek ključavnice: 3 mm dvojni nastavek      |
| Plošča za kableske uvodnice | Velikost: 4<br>Količina: 1   |
| Osnovni material            | Sheet steel  |
| Paketi                      | 1 pc(s).   |
| Neto teža                   | 24,272 kg  |
| Bruto teža                  | 25,8 kg  |
| Carinska tarifna številka   | 94032080   |
| ECLASS 8.0                  | 27180101   |
| Opis izdelka                | AE Compact enclosure, WHD: 400x800x300 mm, Sheet steel, with mounting plate, single-door, with two cam locks |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | DNV<br>Lloyds Register<br>UL + C-UL (listed)              |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |