

# Rittal – The System.

Faster – better – everywhere.



## SE 5831.580

## Sistem samostojećih ohišij SE 8

State: 2.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SE 5831.580 - Sistem samostojećih ohišij SE 8 IP 66/ NEMA 4

Individual sheet steel enclosure with stable enclosure body, two integrated mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible interior installation with the TS 8, enabling full integration into the TS 8 product family. Increased protection due to IP 66 / NEMA 4. Time-saving assembly work due to the roll-formed side panels

## Features

|                              |   |
|------------------------------|---|
| Št. Modela                   | SE 5831.580   |
| Material                     | Ohišje: jeklena pločevina, 1,5 mm<br>Vrata: jeklena pločevina, 2,0 mm<br>Zadnja plošča: jeklena pločevina, 1,5 mm<br>Osnova: jeklena pločevina, 1,5 mm<br>Montažna plošča: jeklena pločevina, 3,0 mm  |
| Površinska obdelava          | Ohišje, vrata in zadnja plošča: temeljni premaz, prašno barvna zunanost, teksturirana barva<br>Montažna plošča: pocinkana<br>Podnožje: temeljni premaz, prašno barvano, teksturirana barva  |
| Barva                        | RAL 7035  |
| Obseg dobave                 | Ohišje, zaprt zgornji del in stranice<br>Vrata<br>Vrata s tečaji na desni, možnost menjave na levo<br>Montažna plošča<br>Podnožje, zaprto<br>Zadnja plošča, snemljiva<br>Ključavnica: 3 mm dvojna ključavnica<br>2 luknjani tirnici TS 18 x 38 mm |
| Mere                         | Širina: 800 mm<br>Višina: 1.800 mm<br>Globina: 400 mm   |
| Mere montažne plošče (Š x V) | 699 mm x 1.696 mm   |
| Razred zaščite po IEC 60 529 | IP 66   |

# Features

---

|                           |   |
|---------------------------|---|
| Razred zaščite NEMA       | NEMA 4<br>NEMA 3R   |
| Število vrat              | 1   |
| Osnovni material          | Sheet steel   |
| Paketi                    | 1 pc(s).  |
| Neto teža                 | 121,1 kg  |
| Bruto teža                | 124,8 kg  |
| Carinska tarifna številka | 94032080  |
| ECLASS 8.0                | 27180101  |
| Opis izdelka              | SE Free-standing enclosure system, WHD: 800x1800x400 mm, Sheet steel, IP 66 / NEMA 4, with mounting plate, single door at the front |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | UL + C-UL (listed)  |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |